

# EZ-RO™ 375/50ATM-BL BLENDED REVERSE OSMOSIS SYSTEM

System Part Number: EV9975-75

Leveraging proprietary technology (CRIT) 15inch 1/2" ID hose optimized water line to equipment

EZ-RO 375/50ATM-BL  
wall mount

EZ-RO 375/50ATM-BL  
with optional  
floor stand bracket

built-in TDS meter allow customized TDS for optimum extraction and taste profile for espresso, coffee and tea\*

4CM cartridge provides calcium and magnesium for improved extraction

Sealed atmospheric storage tank provides compact capacity and electronic pump delivers optimized water to downstream equipment

Pressure gauge allows monitoring of RO inlet pressure and prefilter condition

Built-in bypass, sample port and flush valves speed up installation and cartridge replacement

Feed water connection to system—should be COLD only. Tempered water up to 80°F (26.6°C) can be used.

Do not exceed system specifications for temperature and pressure.

Provide a dedicated feed water supply connection of at least 3/8" inner diameter.

Proprietary Fibredyne™ II filtration media effectively inhibits growth of bacteria on the filter media that can decrease product life. Also can reduce sediment and chlorine to help protect the RO membrane\*

High flow 1/2" ID hose optimized water line to equipment

Installation kit comes complete with tubing, fittings, and mounting hardware for installation

High efficiency RO membrane saves up to two times more water than standard RO membranes†

Numerous patents pending on blending technology and other aspects of the product design

Allow 3" clearance below system for filter cartridge removal and replacement.

Detailed, illustrated installation guide is included with each system.



United States |